

PRODUCT INFORMATION PACKET



Model No: P327M2

Catalog No: P327M2

10 HP Close-Coupled Pump Motor, 1 phase, 3600 RPM, 230 V, 215JP Frame, ODP
Close-Coupled Pump Motors



Regal and Century are trademarks of Regal Rexnord Corporation or one of its affiliated companies.
©2021 Regal Rexnord Corporation, All Rights Reserved. MC017097E






Nameplate Specifications

Output HP	10 Hp	Output KW	7.5 kW
Frequency	60 Hz	Voltage	230 V
Current	37.5 A	Speed	3510 rpm
Service Factor	1.15	Phase	1
Duty	Continuous	Insulation Class	F
Frame	215JP	Enclosure	Open Drip Proof
Thermal Protection	No	Ambient Temperature	40 °C
UL	Recognized	CSA	Y
Number of Speeds	1		

Technical Specifications

Electrical Type	Capacitor Start Capacitor Run	Starting Method	Across The Line
Poles	2	Rotation	Counterclockwise
Mounting	Rigid Base	Drive End Bearing	Ball
Opp Drive End Bearing	Ball	Frame Material	Rolled Steel
Shaft Type	Keyed	Overall Length	25.04 in
Frame Length	12.40 in	Shaft Diameter	1.750 in
Shaft Extension	8.43 in		
Connection Drawing	A-EE9048MF-CY	Outline Drawing	037644CY


This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:10/07/2021




DRAWN	GR 07/25/12
CHK	SR 07/25/12
APPD	
SCALE	1=5
REF	037644
FMF	
PREV	

NO.	REVISION	BY & DATE	CHK	ANG	±7'30"	FINISH				PREV	
THIS DRAWING IN DESIGN AND DETAIL IS OUR PROPERTY AND MUST NOT BE USED EXCEPT IN CONNECTION WITH OUR WORK ALL RIGHTS OF DESIGN AND INVENTION ARE RESERVED THIS IS AN ELECTRONICALLY GENERATED DOCUMENT – DO NOT SCALE THIS PRINT			RFP			CAD FILE 037644CY		SIZE	DRAWING NO.	PAGE OF	REV.
			DIST LB					A	037644CY		


C.W. ROTATION



C.C.W. ROTATION



SINGLE VOLTAGE
CAPACITOR START
CAPACITOR RUN
REVERSIBLE



VIEW OF TERMINAL END

			✓ MAX. SURFACE ROUGHNESS UNLESS NOTED OTHERWISE		UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOL. ON XX± XXX±.005 XXXX±.0005 ANGLES±			
			MATL SPEC		180 - 210 SWITCH		DRAWN BY GK	11-01-1986
			FINISH		MARATHON ELECTRIC		CHKD BY ML	11-01-1986
1 11-04-1986 NEW DRAWING			REFERENCE DRW.		WAUSAU, WISCONSIN 54401		APPD BY FG	11-04-1986
CN 7664C			GK		PART NAME CONNECTION DIAGRAM		DRWG NO A- EE9048MF	
REV	DATE	CHANGE	NAME		CADD FILE NO.		EE9048MF	

SHOP BOOK

PURCHASED

DISTRIBUTION - WA - LB - WP - LM - BR

CADD FILE NO.

EE9048MF